



MASTER PL-T TOP 4 Pin

MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp
Compact long-arc low-pressure mercury discharge lamp
Envelope consists of 6 parallel narrow fluorescent tubes
Amalgam controlled operation

Product data

General Information	
Cap base	GX24Q-2 [GX24q-2]
Life to 50% failures preheat (nom.)	13000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Colour Code	830 [CCT of 3,000 K]
Lamp Luminous Flux 25°C EL (Nom)	1200 lm
Lamp Luminous Flux (Nom)	1200 lm
Colour Designation	Warm white (WW)
Colour Temperature, horizontal (Nom)	3000 K
Lamp Luminous Efficacy EM (Min)	67 lm/W
Colour Rendering Index, horiz (Nom)	>80
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	85 %
LLMF 8000 h Rated	84 %

LLMF 12000 h Rated	81 %
Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp current (nom.)	0.220 A
Temperature	
Design temperature (nom.)	28 °C
Controls and Dimming	
Dimmable	yes
Mechanical and Housing	
Cap base information	4P
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	21 kWh

MASTER PL-T TOP 4 Pin

Product Data

Full product code	871150088908970
Order product name	MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX
EAN/UPC – product	8711500889089
Order code	927910883069
Local Code	PLTT18W8304PA
Numerator – quantity per pack	1

Numerator – packs per outer box	50
Material no. (12NC)	927910883069
Net weight (piece)	58.000 g
ILCOS Code	FSM-18/30/1B-E-GX24q=2

Warnings and Safety

Dimensional drawing


□

Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 18W/830/4P 1CT/ 5X10BOX	41 mm	71.7 mm	96.0 mm	111.7 mm

PL-T TOP 18W/830/4P A

Photometric data

⊙




Lightcolour /830

Lightcolour /830


MASTER PL-T TOP 4 Pin

Lifetime



LDLM_PLTTOP4P_0001-Lumen maintenance diagram

LDLE_PLTTOP4P_0001-Life expectancy diagram



LDLE_PLTTOP4P_0002-Life expectancy diagram

