



MASTER PL-T TOP 4 Pin

MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	GX24Q-2 [GX24q-2]
Flux measurement reference	Sphere

Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,160 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (Rated) (Min)	67 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Power Consumption	18.7 W
Lamp Current (Nom)	0.220 A

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	19 kWh
EPREL Registration Number	423324

MASTER PL-T TOP 4 Pin

Product Data	
Order product name	MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX
Full product name	MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX
Full product code	871150088908970
Local code description	PLTT18W8304P
Order code	927910883069
Material Nr. (12NC)	927910883069


Local order code	PLTT18W8304P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500889089
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500889409

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX	41 mm	71.7 mm	96.0 mm	111.7 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX

MASTER PL-T TOP 4 Pin


Lifetime



Lumen Maintenance Diagram - MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 18W/830/4P 1CT/5X10BOX

