



MASTER PL-T TOP 4 Pin

MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


| General Information | | Operating and Electrical | |
|------------------------------------|--------------------|-------------------------------|---------|
| Cap-Base | GX24Q-2 [GX24q-2] | Power Consumption | 18.7 W |
| Flux measurement reference | Sphere | Lamp Current (Nom) | 0.220 A |
| Light Technical | | Controls and Dimming | |
| Color Code | 840 [CCT of 4000K] | Dimmable | Yes |
| Luminous Flux | 1,160 lm | Approval and Application | |
| Color Designation | Cool White (CW) | Energy Efficiency Class | G |
| Chromaticity Coordinate X (Nom) | 0.38 | Mercury (Hg) Content (Max) | 1.4 mg |
| Chromaticity Coordinate Y (Nom) | 0.38 | Mercury (Hg) Content (Nom) | 1.4 mg |
| Correlated Color Temperature (Nom) | 4000 K | Energy Consumption kWh/1000 h | 19 kWh |
| Luminous Efficacy (Rated) (Min) | 67 lm/W | EPREL Registration Number | 423325 |
| Color rendering index (CRI) | 80 | | |

MASTER PL-T TOP 4 Pin

| Product Data | |
|------------------------|--|
| Order product name | MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX |
| Full product name | MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX |
| Full product code | 871150088941670 |
| Local code description | PLTT18W8404P |
| Order code | 927910884069 |
| Material Nr. (12NC) | 927910884069 |


| | |
|---------------------------------|---------------|
| Local order code | PLTT18W8404P |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500889416 |
| Numerator - Packs per outer box | 50 |
| EAN/UPC - Case | 8711500889430 |

Dimensional drawing



| Product | D (max) | A (max) | B (max) | C (max) |
|--|---------|---------|---------|----------|
| MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX | 41 mm | 71.7 mm | 96.0 mm | 111.7 mm |


Photometric data




Spectral Power Distribution Colour - MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX

MASTER PL-T TOP 4 Pin


Lifetime



Lumen Maintenance Diagram - MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 18W/840/4P 1CT/5X10BOX

