



# PL-T Triple 4-Pin Base

## PL-T 32W/835/A/4P/ALTO 1BL/6

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information		
Cap-Base	GX24Q-3 [GX24q-3]	
Lamp Current (Nom)		0.320 A
Controls and Dimming		
Dimmable	Yes	
Approval and Application		
Mercury (Hg) Content (Nom)	1.4 mg	
Product Data		
Order product name	PL-T 32W/835/A/4P/ALTO 1BL/6	
Full product name	PL-T 32W/835/A/4P/ALTO 1BL/6	
Order code	465922	
Material Nr. (12NC)	927911083502	
Numerator - Quantity Per Pack	1	


Light Technical	
Color Code	835 [CCT of 3500K]
Luminous Flux	2,250 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	68.2 lm/W
Color rendering index (CRI)	82

Operating and Electrical	
Power Consumption	33.0 W

# PL-T Triple 4-Pin Base


EAN/UPC - Product/Case	046677465926
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677465921

## Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
PL-T 32W/835/A/4P/ALTO 1BL/6	1-5/8 inch	3-15/16 inch	4-7/8 inch	5-1/2 inch

## Photometric data




Spectral Power Distribution Colour - PL-T 32W/835/A/4P/ALTO 1BL/6

## Lifetime




Lumen Maintenance Diagram - PL-T 32W/835/A/4P/ALTO 1BL/6



Life Expectancy Diagram - PL-T 32W/835/A/4P/ALTO 1BL/6

## PL-T Triple 4-Pin Base

### Lifetime



Life Expectancy Diagram - PL-T 32W/835/A/4P/ALTO 1BL/6

