



MASTER PL-T TOP 4 Pin



MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap base	GX24Q-3 [GX24q-3]	Power Consumption	28.3 W
Flux measurement reference	Sphere	Lamp current (nom.)	0.335 A
Light Technical		Controls and Dimming	
Colour Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	1,830 lm	Approval and Application	
Colour designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) content (max.)	1.4 mg
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) content (nom.)	1.4 mg
Correlated Colour Temperature	4000 K	Energy consumption kWh/1,000 hours	29 kWh
Luminous efficacy (rated) (min.)	66 lm/W	EPREL registration number	423327
Colour rendering index (CRI)	80		

MASTER PL-T TOP 4 Pin

Product Data	
Order product name	MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX
Full EOC	871150088947870
Order code	88947870
Material no. (12 NC)	927911384069
Local order code	26PLT8404PINTOP


SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500889478
Numerator – packs per outer box	50
EAN/UPC – Case	8711500889492

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX	41 mm	86.7 mm	111.0 mm	126.7 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX

MASTER PL-T TOP 4 Pin


Lifetime



Lumen Maintenance Diagram - MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX

