



# MASTER PL-T TOP 4 Pin

## MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	GX24Q-3 [GX24q-3]
Flux measurement reference	Sphere
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	1,830 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	66 lm/W
Color rendering index (CRI)	80


Operating and Electrical	
Power Consumption	28.3 W
Lamp Current (Nom)	0.335 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	29 kWh
EPREL Registration Number	423327

MASTER PL-T TOP 4 Pin

Product Data	
Order product name	MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX
Full product code	871150088947870
Order code	927911384069
Material Nr. (12NC)	927911384069
Local order code	PLTT26W8404PA


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500889478
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500889492

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX	41 mm	86.7 mm	111.0 mm	126.7 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX

MASTER PL-T TOP 4 Pin


Lifetime



Lumen Maintenance Diagram - MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T TOP 26W/840/4P 1CT/5X10BOX

