



MASTER PL-T TOP 4 Pin

MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes. Amalgam controlled operation

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- · Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical			
Cap-Base	GX24q-3	Power Consumption	34.5 W		
Flux measurement reference	Sphere	Lamp Current (Nom)	0.320 A		
Light Technical		Controls and Dimming			
Color Code	840 [CCT of 4000K]	Dimmable	Yes		
Luminous Flux	2,300 lm				
Color Designation	Cool White (CW)	Approval and Application	Approval and Application		
Chromaticity Coordinate X (Nom)	0.38	Energy Efficiency Class	G		
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Max)	1.4 mg		
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Nom)	1.4 mg		
Luminous Efficacy (Rated) (Min)	75 lm/W	Energy Consumption kWh/1000 h	35 kWh		
Color rendering index (CRI)	80	EPREL Registration Number	423329		

MASTER PL-T TOP 4 Pin

Product Data	
Order product name	MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX
Full product code	871150056026170
Local code description	PLTT32W8404P
Order code	927911984069
Material Nr. (12NC)	927911984069


Local order code	PLTT32W8404P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500560261
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500610034

Dimensional drawing



Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX	41 mm	98.7 mm	123.0 mm	138.7 mm


Photometric data




Spectral Power Distribution Colour - MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX


MASTER PL-T TOP 4 Pin

Lifetime



Lumen Maintenance Diagram - MASTER PL-T TOP 32W/840/4P 1CT/ 5X10BOX





Life Expectancy Diagram - MASTER PL-T TOP 32W/840/4P 1CT/5X10BOX



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.