



MASTER PL-T Xtra 4 Pin



MASTER PL-T XTRA 32W/840/4P 1CT/5X10BOX

Energy saving compact fluorescent lamp. Compact long-arc low-pressure mercury discharge lamp. Envelope consists of 6 parallel narrow fluorescent tubes

Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	GX24q-3
Flux measurement reference	Sphere
Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	2,300 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	75 lm/W
Colour rendering index (CRI)	80


Operating and Electrical	
Power Consumption	32.0 W
Lamp current (nom.)	0.320 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	3 mg
Mercury (Hg) content (nom.)	3.0 mg
Energy consumption kWh/1,000 hours	32 kWh
EPREL registration number	423336

MASTER PL-T Xtra 4 Pin

Product Data	
Order product name	MASTER PL-T Xtra 32W/840/4P 1CT/5X10BOX
Full product name	MASTER PL-T XTRA 32W/840/4P 1CT/5X10BOX
Full EOC	871150089743570
Order code	89743570
Material no. (12 NC)	927912584014
Local order code	32PLT8404PXTRA


SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500897435
Numerator – packs per outer box	50
EAN/UPC – Case	8711500897459

Dimensional drawing




Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T Xtra 32W/840/4P 1CT/5X10BOX	41.0 mm	98.7 mm	123.0 mm	138.7 mm

Photometric data




Spectral Power Distribution Colour - MASTER PL-T Xtra 32W/840/4P 1CT/5X10BOX

Lifetime





Life Expectancy Diagram - MASTER PL-T Xtra 32W/840/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T Xtra 32W/840/4P 1CT/5X10BOX

MASTER PL-T Xtra 4 Pin

Lifetime



Life Expectancy Diagram - MASTER PL-T Xtra 32W/840/4P 1CT/5X10BOX

Lumen Maintenance Diagram - MASTER PL-T Xtra 32W/840/4P 1CT/5X10BOX

