



MASTER PL-T 4 Pin 4-針腳型

MASTER PL-T 18W/830/4P 1CT/5X10BOX

省電型精巧螢光燈管。精巧型長電弧低壓水銀放電燈管。套管內含 6 個平行細長螢光燈管

安全提示

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	GX24Q-2 [GX24q-2]
通量測量參考	Sphere
照明技術	
色碼	830 [CCT of 3000K]
光通量	1,150 lm
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.44
色度坐標 Y (Nom)	0.403
相關色彩溫度 (規範)	3000 K
流明功能 (額定) (最小)	67 lm/W
演色性指數 (CRI)	80
運轉與電力	
耗電量	18.0 W


燈具電流 (標稱)	0.225 A
控制與調光	
可調光	是
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	1.4 mg
汞 (Hg) 含量 (標稱)	1.4 mg
能源消耗 kWh/1000 h	18 kWh
EPREL 註冊碼	423342
產品資料	
下訂產品名稱	MASTER PL-T 18W/830/4P 1CT/5X10BOX
完整產品名稱	MASTER PL-T 18W/830/4P 1CT/5X10BOX
完整產品代碼	871150061076870

MASTER PL-T 4 Pin 4-針腳型

訂單代碼	927914483071
材質 Nr. (12NC)	927914483071
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500610768


分子 - 每一外盒包裝	50
EAN/UPC - 箱	8711500610966

二维绘图




Product	D (max)	A (max)	B (max)	C (max)
MASTER PL-T 18W/830/4P 1CT/5X10BOX	41.0 mm	71.7 mm	96.0 mm	111.7 mm

光度数据




Spectral Power Distribution Colour - MASTER PL-T 18W/830/4P 1CT/5X10BOX

壽命




Life Expectancy Diagram - MASTER PL-T 18W/830/4P 1CT/5X10BOX



Life Expectancy Diagram - MASTER PL-T 18W/830/4P 1CT/5X10BOX

MASTER PL-T 4 Pin 4-針腳型

壽命



Lumen Maintenance Diagram - MASTER PL-T 18W/830/4P 1CT/5X10BOX

