



# TL-D LIFEMAX Super 80 JIS

## TL-D 18W/865 JIS 1SL/25

The TL-D LIFEMAX Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires. The lamp is complying with Japanese Industrial Standard.

### Product data

General Information	
Cap-Base	G13 [ Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h
Life to 50% Failures Preheat (Nom)	20000 h

  

Light Technical	
Color Code	865 [ CCT of 6500K]
Luminous Flux (Nom)	1350 lm
Color Designation	Cool Daylight
Lumen Maintenance 2000 h (Nom)	96 %
Lumen Maintenance 5000 h (Nom)	94 %
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Rendering Index (Nom)	80

  

Operating and Electrical	
Power (Nom)	19 W
Lamp Current (Nom)	0.35 A
Voltage (Nom)	65 V

Controls and Dimming	
Dimmable	No

  

Mechanical and Housing	
Cap-Base Information	Green Cap

  

Approval and Application	
Mercury (Hg) Content (Nom)	2.0 mg

  

Product Data	
Full product code	871150062995101
Order product name	TL-D 18W/865 JIS 1SL/25
EAN/UPC - Product	8711500629951
Order code	927919986532
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927919986532
Net Weight (Piece)	0.080 kg

# TL-D LIFEMAX Super 80 JIS

## Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 18W/865 JIS 1SL/25	28 mm	581.3 mm	588.4 mm	585.8 mm	595.5 mm

TL-D 18W/865 JIS

