PHILIPS

Lighting



MASTER TL-D Super 80 日光燈管

MASTER TL-D Super 80 58W/830 1SL/25

直徑 26 mm 的螢光燈管

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
通量測量參考	Sphere
壽命 (故障率 50%) (標稱)	15,000 h

照明技術	
色碼	830 [CCT of 3000K]
光通量	5,240 lm
色彩名稱	暖白光 (WW)
色度坐標 X (標稱)	0.44
色度坐標 Y (Nom)	0.403
相關色彩溫度 (規範)	3000 K
光效 (額定) (標準)	90 lm/W
演色性指數 (CRI)	82

運轉與電力	
耗電量	59.4 W
燈具電流 (標稱)	0.670 A

控制與調光	
可調光	是

機械與外罩	
燈泡形狀	T8 [26 mm (T8)]


認證與應用	
節能省電等級	G
汞 (Hg) 含量 (標稱)	1.7 mg
能源消耗 kWh/1000 h	60 kWh
EPREL 註冊碼	423394

產品資料	
下訂產品名稱	MASTER TL-D Super 80 58W/830 1SL/25
完整產品名稱	MASTER TL-D Super 80 58W/830 1SL/25
完整產品代碼	871150063213540
訂單代碼	927922083023
材質 Nr. (12NC)	927922083023
分子 - 每個包裝的數量	1

MASTER TL-D Super 80 日光燈管


EAN/UPC - 產品/案例	8711500632135
分子 - 每一外盒包裝	25
EAN/UPC - 箱	8711500632142

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Super 80 58W/830 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

光度数据




Spectral Power Distribution Colour - MASTER TL-D Super 80 58W/830 1SL/25

壽命



Life Expectancy Diagram - MASTER TL-D Super 80 58W/830 1SL/25



Life Expectancy Diagram - MASTER TL-D Super 80 58W/830 1SL/25

MASTER TL-D Super 80 日光燈管

壽命

Lumen Maintenance Diagram - MASTER TL-D Super 80 58W/830 1SL/25

© 2023 Signify Holding 保留一切權利。 Signify 不對本協議所含括資訊之準確性及完整性提供任何聲明或保證，對以此訊息為依據採取的任何行動亦概不負責。 除非 Signify 同意，本文件提及之資訊並非任何商業合約，亦不構成任何報價或合約任一部分。 Philips 與 Philips Shield Emblem 均屬 Koninklijke Philips N.V 註冊商標。