



# MASTER TL-D Secura

## MASTER TL-D Secura 58W/840 SLV/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

### Warnings and Safety

- Not suitable for closed luminaires (as indicated by two blue rings)
- Recommended use in combination with self-stopping lamp control system
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- It's strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

### Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Flux measurement reference	Sphere
Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	5,100 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	85.5 lm/W
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	59.4 W

Lamp Current (Nom)	0.670 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T8
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.7 mg
Energy Consumption kWh/1000 h	60 kWh
EPREL Registration Number	423411
Product Data	
Order product name	MASTER TL-D Secura 58W/840 SLV/25
Full product name	MASTER TL-D Secura 58W/840 SLV/25

MASTER TL-D Secura

Full product code	871150064018540
Order code	927922484076
Material Nr. (12NC)	927922484076
Local order code	TLD58W840SECUR
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500640185
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500640192

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Secura 58W/840 SLV/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Secura 58W/840 SLV/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Secura 58W/840 SLV/25



Life Expectancy Diagram - MASTER TL-D Secura 58W/840 SLV/25

MASTER TL-D Secura

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Secura 58W/840 SLV/25

