



# Eco passport

MASTER TL-D Super 80

MASTER TL-D Super 80 70W/830 SLV/25



## Energy

- Power (Rated) (Nom) : 70.0 W
- Luminous Efficacy (rated) (Nom) : 89 lm/W
- Energy Efficiency Label (EEL) : A
- Dimmable : Yes



## Substances

- Mercury (Hg) Content (Nom) : 3.0 mg



## Lifetime

- Life To 10% Failures (Nom) : 12000 h
- Life to 50% Failures (Nom) : 15000 h
- Life to 50% Failures Preheat (Nom) : 20000 h

### Our environmental product specifications overview

At Philips, we strive to make the world healthier and more sustainable through innovation. Our sustainability efforts are globally recognised and reflected, e.g. by our continuous leading positions global rankings like the Dow Jones Sustainability Index and the Carbon Disclosure Project. In our eco-design process we focus on Energy, Weight, Recycling, Packaging, Substances and Reliability to view and further improve the environmental performance of our products.

# PHILIPS

2018, July 11

data subject to change

Order code : 927923883014