



MASTER TL-D HF Super 80 日光燈管

MASTER TL-D HF Super 80 32W/840 SLV/25

直徑 26 mm 的螢光燈管與氬氣充填

安全提示

- Special electronic gear must be used
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G13 [Medium Bi-Pin Fluorescent]
測量測量參考	Sphere
照明技術	
色碼	840 [CCT of 4000K]
光通量	3,120 lm
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	0.38
色度坐標 Y (Nom)	0.38
相關色彩溫度 (規範)	4000 K
光效 (額定) (標準)	100 lm/W
演色性指數 (CRI)	82
運轉與電力	
耗電量	32.4 W
燈具電流 (標稱)	0.255 A


控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T8
認證與應用	
節能省電等級	F
汞 (Hg) 含量 (標稱)	1.7 mg
能源消耗 kWh/1000 h	33 kWh
EPREL 註冊碼	423438
產品資料	
下訂產品名稱	MASTER TL-D HF Super 80 32W/840 SLV/25
完整產品名稱	MASTER TL-D HF Super 80 32W/840 SLV/25
完整產品代碼	871150063153440
訂單代碼	927924584023
材質 Nr. (12NC)	927924584023

MASTER TL-D HF Super 80 日光燈管

分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500631534
分子 - 每一外盒包裝	25


EAN/UPC - 箱	8711500631541
-------------	---------------

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D HF Super 80 32W/840 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

光度数据




Spectral Power Distribution Colour - MASTER TL-D HF Super 80 32W/840 SLV/25

壽命




Life Expectancy Diagram - MASTER TL-D HF Super 80 32W/840 SLV/25



Life Expectancy Diagram - MASTER TL-D HF Super 80 32W/840 SLV/25

MASTER TL-D HF Super 80 日光燈管

壽命



Lumen Maintenance Diagram - MASTER TL-D HF Super 80 32W/840 SLV/25

