



MASTER TL-D 高频超级 80

MASTER TL-D HF Super 80 50W/830 SLV/25

直径 26mm 的低压气体放电灯，内充氙气

安全提示

- Special electronic gear must be used
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


产品数据

一般信息	
底盖	G13 [Medium Bi-Pin Fluorescent]
灯技术	
颜色代码	830 [CCT of 3000K]
光通量	5,000 lm
颜色名称	暖白色 (WW)
相关色温 (标称)	3000 K
光效 (额定) (标称)	100 lm/W
显色指数 (CRI)	>80
操作和电气	
功耗	50.0 W
灯具电流 (标称)	0.355 A
控制和调光	
可调光	是

机械和外壳	
灯泡外形	T8 [26 毫米 (T8)]
审批和申请	
汞 (Hg) 含量 (标称)	2.0 mg
能耗 kWh/1000 h	58 kWh
产品数据	
订单产品名称	MASTER TL-D HF Super 80 50W/830 SLV/25
完整的产品名称	MASTER TL-D HF Super 80 50W/830 SLV/25
完整产品代码	871150063156540
订购代码	927925083014
材料编号 (12NC)	927925083014
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500631565
计算器 - 每个外包装箱中的包数	25
EAN/UPC - 案例	8711500631572


MASTER TL-D 高频超级 80

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D HF Super 80 50W/830 SLV/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

光度数据




Spectral Power Distribution Colour - MASTER TL-D HF Super 80 50W/830 SLV/25

寿命




Life Expectancy Diagram - MASTER TL-D HF Super 80 50W/830 SLV/25



Life Expectancy Diagram - MASTER TL-D HF Super 80 50W/830 SLV/25

MASTER TL-D 高频超级 80

寿命



Lumen Maintenance Diagram - MASTER TL-D HF Super 80 50W/830
SLV/25

