



T8 Standard

F32T8/TL850/ALTO 25PK

Philips T8 lamps are energy-efficient lighting solutions.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life 12-Hr Programstart [Hrs]	24000 h
Life 12-Hr Instant Start [Hrs]	15000 h
Features	ALTO® (ALTO)

Light Technical	
Color Code	TL850 [CCT of 5000K (850)]
Luminous Flux (Nom)	2850 lm
Color Designation	TL850
Design Mean Lumens	2705 lm
Correlated Color Temperature (Nom)	5000 K
Color Rendering Index (Nom)	80

Operating and Electrical	
Power (Rated) (Nom)	32 W


Mechanical and Housing	
Cap-Base Information	Green Base

Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	30.3 pg/lm.h
Mercury (Hg) Content (Nom)	2.0 mg

Product Data	
Full product code	871869674551900
Order product name	F32T8/TL850/ALTO 25PK
EAN/UPC - Product	8718696745519
Order code	927925485001
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927925485001
Net Weight (Piece)	0.130 kg

T8 Standard

Dimensional drawing



Product

F32T8/TL850/ALTO 25PK

TLD 32W/850 RS

