



TL5 consumer products



TL5 HE 14W WW 1PP/10

A TL5 lamp is 40% thinner and 5 cm shorter than corresponding TL-D lamp. The lamps are available in 3 wattages and in 2 colors (warm white and cool white)

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G5
Features	na [Not Applicable]
Flux measurement reference	Sphere
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,200 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	86 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	14.0 W


Lamp Current (Nom)	0.165 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	T5
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Nom)	1.2 mg
Energy Consumption kWh/1000 h	14 kWh
EPREL Registration Number	423442
Product Data	
Order product name	TL5 HE 14W WW 1PP/10
Full product name	TL5 HE 14W WW 1PP/10
Full product code	871150089717625

TL5 consumer products

Order code	927926083032
Material Nr. (12NC)	927926083032
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500897176


Numerator - Packs per outer box	10
EAN/UPC - Case	8711500897183

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 HE 14W WW 1PP/10	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

Photometric data




Spectral Power Distribution Colour - TL5 HE 14W WW 1PP/10

Lifetime



Life Expectancy Diagram - TL5 HE 14W WW 1PP/10



Life Expectancy Diagram - TL5 HE 14W WW 1PP/10

TL5 consumer products

Lifetime



Lumen Maintenance Diagram - TL5 HE 14W WW 1PP/10

