



# Eco passport

MASTER TL5 High Efficiency

MASTER TL5 HE 14W/830 SLV/40



## Energy

- Power (Rated) (Nom) : 14 W
- Luminous efficacy (@ max. lumen, rated) (nom.) : 99 lm/W
- Lamp Luminous Efficacy EM (Nom) : 86 lm/W
- Energy efficiency label (EEL) : A+
- Dimmable : yes



## Substances

- Mercury (Hg) content (nom.) : 1.4 mg



## Lifetime

- Life to 50% failures preheat (nom.) : 24000 h

### Our environmental product specifications overview

At Philips, we strive to make the world healthier and more sustainable through innovation. Our sustainability efforts are globally recognised and reflected, e.g. by our continuous leading positions global rankings like the Dow Jones Sustainability Index and the Carbon Disclosure Project. In our eco-design process we focus on Energy, Weight, Recycling, Packaging, Substances and Reliability to view and further improve the environmental performance of our products.

# PHILIPS

2018, August 11  
data subject to change  
Order code : 927926083055