



MASTER TL5 High Efficiency 高效率日光燈管

MASTER TL5 HE 14W/830 SLV/40

直徑 16 mm 的螢光燈管

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	G5
功能	na [Not Applicable]
通量測量參考	Sphere
照明技術	
色碼	830 [CCT of 3000K]
光通量	1,200 lm
色彩名稱	暖白光 (WW)
色度坐標 x (標稱)	0.44
色度坐標 y (Nom)	0.403
相關色彩溫度 (規範)	3000 K
光效 (額定) (標準)	86 lm/W
演色性指數 (CRI)	82


運轉與電力	
耗電量	14.0 W
燈具電流 (標稱)	0.165 A
控制與調光	
可調光	是
機械與外罩	
燈泡形狀	T5
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (標稱)	1.2 mg
能源消耗 kWh/1000 h	14 kWh
EPREL 註冊碼	423443

MASTER TL5 High Efficiency 高效率日光燈管

產品資料	
下訂產品名稱	MASTER TL5 HE 14W/830 SLV/40
完整產品名稱	MASTER TL5 HE 14W/830 SLV/40
完整產品代碼	871150063938755
訂單代碼	927926083055
材質 Nr. (12NC)	927926083055


分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500639387
分子 - 每一外盒包裝	40
EAN/UPC - 箱	8711500867469

二维绘图




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 14W/830 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

光度数据




Spectral Power Distribution Colour - MASTER TL5 HE 14W/830 SLV/40

壽命




Life Expectancy Diagram - MASTER TL5 HE 14W/830 SLV/40



Life Expectancy Diagram - MASTER TL5 HE 14W/830 SLV/40

MASTER TL5 High Efficiency 高效率日光燈管

壽命



Lumen Maintenance Diagram - MASTER TL5 HE 14W/830 SLV/40

