



MASTER TL5 High Efficiency

MASTER TL5 HE 28W/827 SLV/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	24000 h
Features	na [Not Applicable]
System Description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	2900 lm
Luminous Flux (Rated) (Nom)	2675 lm
Color Designation	Incandescent White
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	104 lm/W
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	96 lm/W

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Nom)	27.9 W
Lamp Current (Nom)	0.170 A
Temperature	
Design Temperature (Nom)	35 °C


MASTER TL5 High Efficiency

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	Green Plate
Approval and Application	
Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	31 kWh
Product Data	
Full product code	871150064322355

Order product name	MASTER TL5 HE 28W/827 SLV/40
EAN/UPC - Product	8711500643223
Order code	927926582755
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927926582755
Net Weight (Piece)	105.800 g
ILCOS Code	FDH-28/27/1B-L/P-G5-16/1150

Warnings and Safety


Dimensional drawing




TL5 28W/827/GP HE

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 28W/827 SLV/40	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm

Photometric data



LDPB_TL5-HE8_827-Spectral power distribution B/W



LDPO_TL5-HE8_827-Spectral power distribution Colour

MASTER TL5 High Efficiency

Lifetime



LDLE_TL5-HE8_0002-Life expectancy diagram

