



MASTER TL5 High Efficiency

MASTER TL5 HE 28W/830 SLV/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Operating and Electrical	
Cap-Base	G5 [G5]	Power Consumption	28.1 W
Features	na [Not Applicable]	Lamp Current (Nom)	0.170 A
Flux measurement reference	Sphere	Controls and Dimming	
Light Technical		Dimmable	Yes
Color Code	830 [CCT of 3000K]	Mechanical and Housing	
Luminous Flux	2,675 lm	Bulb Shape	T5 [16 mm (T5)]
Color Designation	Warm White (WW)	Approval and Application	
Chromaticity Coordinate X (Nom)	0.44	Energy Efficiency Class	F
Chromaticity Coordinate Y (Nom)	0.403	Mercury (Hg) Content (Nom)	1.2 mg
Correlated Color Temperature (Nom)	3000 K	Energy Consumption kWh/1000 h	29 kWh
Luminous Efficacy (rated) (Nom)	96 lm/W	EPREL Registration Number	423460
Color rendering index (CRI)	82		

MASTER TL5 High Efficiency

Product Data	
Order product name	MASTER TL5 HE 28W/830 SLV/40
Full product name	MASTER TL5 HE 28W/830 SLV/40
Full product code	871150063946255
Order code	927926583055
Material Nr. (12NC)	927926583055


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500639462
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500867582

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 28W/830 SLV/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL5 HE 28W/830 SLV/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HE 28W/830 SLV/40



Life Expectancy Diagram - MASTER TL5 HE 28W/830 SLV/40

MASTER TL5 High Efficiency

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE 28W/830 SLV/40

