



MASTER TL5 High Efficiency



MASTER TL5 HE 28W/840 UNP/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G5 [G5]
Features	na [Not Applicable]
Flux measurement reference	Sphere

Light Technical	
Colour Code	840 [CCT of 4000K]
Luminous Flux	2,675 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	96 lm/W
Colour rendering index (CRI)	80

Operating and Electrical	
Power Consumption	28.1 W
Lamp current (nom.)	0.170 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb shape	T5 [16 mm (T5)]

Approval and Application	
Energy Efficiency Class	F
Mercury (Hg) content (nom.)	1.2 mg
Energy consumption kWh/1,000 hours	29 kWh
EPREL registration number	423535


Product Data	
Order product name	MASTER TL5 HE 28W/840 UNP/40
Full product name	MASTER TL5 HE 28W/840 UNP/40
Full EOC	871150061090455
Local code description	28840IP
Order code	61090455
Material no. (12 NC)	927926584018

MASTER TL5 High Efficiency

Local order code	28840IP
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500610904
Numerator – packs per outer box	40


EAN/UPC - Case	8711500634566
----------------	---------------

Dimensional drawing





Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 28W/840 UNP/40	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm

Photometric data



Spectral Power Distribution Colour - MASTER TL5 HE 28W/840 UNP/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HE 28W/840 UNP/40

Life Expectancy Diagram - MASTER TL5 HE 28W/840 UNP/40

MASTER TL5 High Efficiency

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE 28W/840 UNP/40

