



# MASTER TL5 High Efficiency



# MASTER TL5 HE 28W/865 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

#### **Warnings and Safety**

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### **Product data**

General Information			
Cap-Base	G5		
Features	na [Not Applicable]		
Flux measurement reference	Sphere		
Light Technical			
Color Code	865 [CCT of 6500K]		
Luminous Flux	2,500 lm		
Color Designation	Cool Daylight		
Chromaticity Coordinate X (Nom)	0.313		
Chromaticity Coordinate Y (Nom)	0.337		
Correlated Color Temperature (Nom)	6500 K		
Luminous Efficacy (rated) (Nom)	90 lm/W		
Color rendering index (CRI)	82		
Operating and Electrical			
Power Consumption	28.1 W		
Lamp Current (Nom)	0.170 A		


Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Bulb Shape	T5		
Approval and Application			
Energy Efficiency Class	G		
Mercury (Hg) Content (Nom)	1.2 mg		
Energy Consumption kWh/1000 h	29 kWh		
EPREL Registration Number	423538		
Product Data			
Order product name	MASTER TL5 HE 28W/865 SLV/40		
Full product name	MASTER TL5 HE 28W/865 1SL/40		
Full product code	871150071015455		
Order code	71015455		
Material Nr. (12NC)	927926586555		
Numerator - Quantity Per Pack	1		

Datasheet, 2023, April 14 data subject to change

# **MASTER TL5 High Efficiency**


EAN/UPC - Product/Case	8711500710154		
Numerator - Packs per outer box	40		
EAN/UPC - Case	8711500867612		

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 28W/865	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
SLV/40					


#### Photometric data



Spectral Power Distribution Colour - MASTER TL5 HE 28W/865 SLV/40

## Lifetime






Life Expectancy Diagram - MASTER TL5 HE 28W/865 SLV/40

Life Expectancy Diagram - MASTER TL5 HE 28W/865 SLV/40

# **MASTER TL5 High Efficiency**

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE 28W/865 SLV/40



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.