



MASTER TL5 High Efficiency

MASTER TL5 HE 35W/827 SLV/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Product data

General Information	
Cap base	G5 [G5]
Life to 50% failures preheat (nom.)	24000 h
Features	na [Not Applicable]
System description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %

Light Technical	
Colour Code	827 [CCT of 2,700 K]
Lamp Luminous Flux 25°C EL (Nom)	3650 lm
Lamp Luminous Flux (Nom)	3325 lm
Colour Designation	Incandescent White
Luminous efficacy (@ max. lumen, rated) (nom.)	105 lm/W
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	94 lm/W
Colour Rendering Index,horiz (Max)	85
Colour Rendering Index,horiz (Min)	80
Colour Rendering Index,horiz (Nom)	82

LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Rated) (Nom)	35.5 W
Lamp current (nom.)	0.175 A

Temperature	
Design temperature (nom.)	35 °C

Controls and Dimming	
Dimmable	yes

Mechanical and Housing	
Cap base information	Green Plate

Approval and Application	
Energy efficiency label (EEL)	A+


MASTER TL5 High Efficiency

Mercury (Hg) content (nom.)	1.4 mg
Energy Consumption kWh/1000 h	38 kWh
Product Data	
Full product code	871150064324755
Order product name	MASTER TL5 HE 35W/827 SLV/40
EAN/UPC – product	8711500643247
Order code	927927082755

Numerator – quantity per pack	1
Numerator – packs per outer box	40
Material no. (12NC)	927927082755
Net weight (piece)	127.400 g
ILCOS Code	FDH-35/27/1B-L/P-G5-16/1450

Warnings and Safety


Dimensional drawing




TL5 35W/827/GP HE

Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 35W/827 SLV/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

Photometric data



Lightcolour /827



Lightcolour /827

MASTER TL5 High Efficiency

Lifetime



LDLE_TL5-HE8_0002-Life expectancy diagram

