



# MASTER TL5 High Efficiency

## MASTER TL5 HE 35W/840 SLV/40

This TL5 lamp (tube diameter 16 mm) has a high luminous efficacy, resulting in low energy consumption. The High Efficiency TL5 lamp offers excellent lumen maintenance and good color rendering. Application areas are offices, industry, public and governmental buildings, schools, hospitals and indoor sports lighting.

### Product data

General Information	
Cap-Base	G5 [ G5]
Life to 50% Failures Preheat (Nom)	24000 h
Features	na [ Not Applicable]
System Description	High Efficiency
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Nom)	35.5 W
Lamp Current (Nom)	0.175 A

Temperature	
Design Temperature (Nom)	35 °C

Light Technical	
Color Code	840 [ CCT of 4000K]
Luminous Flux (Nom)	3650 lm
Luminous Flux (Rated) (Nom)	3325 lm
Color Designation	Cool White (CW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	105 lm/W
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	104 lm/W

# MASTER TL5 High Efficiency

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Cap-Base Information	Green Plate
----------------------	-------------

## Approval and Application

Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	38 kWh

## Product Data

Full product code	871150063952355
-------------------	-----------------

Order product name	MASTER TL5 HE 35W/840 SLV/40
EAN/UPC - Product	8711500639523
Order code	927927084055
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927927084055
Net Weight (Piece)	127.400 g
ILCOS Code	FDH-35/40/1B-L/P-G5-16/1450

## Warnings and Safety


## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE 35W/840 SLV/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

## TL5 HE 35W/840/GP

## Photometric data



LDPB\_TL5-HE8\_840-Spectral power distribution B/W



LDPO\_TL5-HE8\_840-Spectral power distribution Colour

# MASTER TL5 High Efficiency

## Lifetime



LDLE\_TL5-HE8\_0001-Life expectancy diagram

LDLE\_TL5-HE8\_0002-Life expectancy diagram



LDLM\_TL5-HE8\_0001-Lumen maintenance diagram

