



MASTER TL5 HE Secura

MASTER TL5 HE Secura 35W/840 UNP/40

This TL5 High Efficiency Secura lamp (tube diameter 16 mm) has a protective coating that keeps glass and lamp components together in the event of accidental breakage. The lamp is easily identifiable by a blue ring at one end. Application areas are all places where glass shatters can disturb operations and can have an impact on product and people safety, e.g. the food and beverage industry. This lamp is compliant with HACCP regulations and supports HACCP certification.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- It's strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Product data


General Information		Operating and Electrical	
Cap base	G5 [G5]	Power Consumption	35.5 W
		Lamp current (nom.)	0.175 A
Light Technical		Controls and Dimming	
Colour Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	3,650 lm	Mechanical and Housing	
Colour designation	Cool White (CW)	Bulb shape	T5 [16 mm (T5)]
Correlated Colour Temperature	4000 K	Approval and Application	
Luminous efficacy (rated) (nom.)	94 lm/W	Mercury (Hg) content (nom.)	1.4 mg
Colour rendering index (CRI)	82		

MASTER TL5 HE Secura

Energy consumption kWh/1,000 hours	38 kWh
Product Data	
Order product name	MASTER TL5 HE Secura 35W/840 UNP/40
Full product name	MASTER TL5 HE Secura 35W/840 UNP/40
Full EOC	871150095219655
Order code	95219655

Material no. (12 NC)	927927184018
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500952196
Numerator – packs per outer box	40
EAN/UPC - Case	8711500952202

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Secura 35W/840 UNP/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HE Secura 35W/840 UNP/40

Lifetime




Life Expectancy Diagram - MASTER TL5 HE Secura 35W/840 UNP/40



Life Expectancy Diagram - MASTER TL5 HE Secura 35W/840 UNP/40

MASTER TL5 HE Secura

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HE Secura 35W/840 UNP/40

