PHILIPS

Lighting



MASTER TL5 High Output



MASTER TL5 HO 49W/830 UNP/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G5 [G5]
Features	na [Not Applicable]
Flux measurement reference	Sphere

Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	4,375 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.44
Chromaticity Coordinate Y (Nom)	0.403
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	89 lm/W
Colour rendering index (CRI)	82

Operating and Electrical	
Power Consumption	49.3 W
Lamp current (nom.)	0.255 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb shape	T5 [16 mm (T5)]


Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.2 mg
Energy consumption kWh/1,000 hours	50 kWh
EPREL registration number	423545

Product Data	
Order product name	MASTER TL5 HO 49W/830 UNP/40
Full product name	MASTER TL5 HO 49W/830 UNP/40
Full EOC	871150063752955
Order code	63752955
Material no. (12 NC)	927927583018
SAP numerator – quantity per pack	1

MASTER TL5 High Output


EAN/UPC — Product/Case	8711500637529
Numerator – packs per outer box	40
EAN/UPC - Case	8711500637536

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 49W/830 UNP/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 49W/830 UNP/40

Lifetime




Life Expectancy Diagram - MASTER TL5 HO 49W/830 UNP/40



Life Expectancy Diagram - MASTER TL5 HO 49W/830 UNP/40

MASTER TL5 High Output

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 49W/830 UNP/40

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.