



MASTER TL5 High Output Secura

MASTER TL5 HO Secura 49W/840 UNP/40

This TL5 High Output Secura lamp (tube diameter 16 mm) has a protective coating that keeps glass and lamp components together in the event of accidental breakage. The lamp is easily identifiable by a blue ring at one end. Application areas are all places where glass shatters can disturb operations and can have an impact on product and people safety, e.g. the food and beverage industry. This lamp is compliant with HACCP regulations and supports HACCP certification.

Product data

General Information	
Cap-Base	G5 [G5]
Life to 50% Failures Preheat (Nom)	30000 h
System Description	High Output
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	97 %
LSF Preheat 20000 h Rated	84 %
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux (Nom)	4375 lm
Luminous Flux (Rated) (Nom)	4375 lm
Color Designation	Cool White (CW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	99 lm/W
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	89 lm/W

Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical	
Power (Nom)	49.2 W
Lamp Current (Nom)	0.255 A


Temperature	
Design Temperature (Nom)	35 °C

MASTER TL5 High Output Secura

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	Green Plate
Approval and Application	
Energy Efficiency Label (EEL)	A+
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	54 kWh
Product Data	
Full product code	871150095227155

Order product name	MASTER TL5 HO Secura 49W/840 UNP/40
EAN/UPC - Product	8711500952271
Order code	927927684018
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927927684018
Net Weight (Piece)	132.000 g
ILCOS Code	FDH-49/40/1B-L/P-G5-16/1450

Dimensional drawing




Product


MASTER TL5 HO Secura 49W/840 UNP/40

TL5 HO Secura 49W/840

Photometric data



LDPB_TL5HO8SE_840-Spectral power distribution B/W



LDPO_TL5HO8SE_840-Spectral power distribution Colour


MASTER TL5 High Output Secura

Lifetime



LDLE_TL5HO8SE_0001-Life expectancy diagram

LDLE_TL5HO8SE_0002-Life expectancy diagram



LDLM_TL5HO8SE_0001-Lumen maintenance diagram

