



# MASTER TL5 High Output Xtra



## MASTER TL5 HO Xtra 49W/840 1SL/20

Low-pressure high-output mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- Philips HF Xtreme gear ensures longest lifetime.
- To achieve lifetimes as published for 100% operation, dimming below 30% should not be applied.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap-Base	G5
Flux measurement reference	Sphere

Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	4,375 lm
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	89 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Power Consumption	50.0 W

Lamp Current (Nom)	0.255 A
--------------------	---------

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5

Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) Content (Max)	3 mg
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	50 kWh
EPREL Registration Number	423551


Product Data	
Order product name	MASTER TL5 HO Xtra 49W/840 SLV/20

# MASTER TL5 High Output Xtra

Full product name	MASTER TL5 HO Xtra 49W/840 1SL/20
Full product code	871150026253005
Order code	26253005
Material Nr. (12NC)	927927784026
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500262530
Numerator - Packs per outer box	20
EAN/UPC - Case	8711500262608

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO Xtra 49W/840 SLV/20	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO Xtra 49W/840 SLV/20

## Lifetime





Life Expectancy Diagram - MASTER TL5 HO Xtra 49W/840 SLV/20



Life Expectancy Diagram - MASTER TL5 HO Xtra 49W/840 SLV/20

# MASTER TL5 High Output Xtra

## Lifetime



Life Expectancy Diagram - MASTER TL5 HO Xtra 49W/840 SLV/20

Lumen Maintenance Diagram - MASTER TL5 HO Xtra 49W/840 SLV/20

