



# MASTER TL5 High Output



# MASTER TL5 HO 24W/830 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

#### **Warnings and Safety**

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### **Product data**

General Information				
Cap base	G5 [G5]			
Features	na [Not Applicable]			
Flux measurement reference	Sphere			
Light Technical				
Colour Code	830 [CCT of 3000K]			
Luminous Flux	1,700 lm			
Colour designation	Warm White (WW)			
Chromaticity Coordinate X (Nom)	0.44			
Chromaticity Coordinate Y (Nom)	0.403			
Correlated Colour Temperature	3000 K			
Luminous efficacy (rated) (nom.)	76 lm/W			
Colour rendering index (CRI)	82			
Operating and Electrical				
Power Consumption	22.7 W			
Lamp current (nom.)	0.295 A	0.295 A		

Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Bulb shape	T5 [16 mm (T5)]		
Approval and Application			
Energy Efficiency Class	G		
Mercury (Hg) content (nom.)	1.2 mg		
Energy consumption kWh/1,000 hours	23 kWh		
EPREL registration number	423553		
Product Data			
Order product name	MASTER TL5 HO 24W/830 SLV/40		
Full product name	MASTER TL5 HO 24W/830 1SL/40		
Full EOC	871150063958555		
Order code	63958555		
Material no. (12 NC)	927928083055		
Local order code	24830		


Datasheet, 2023, April 16 data subject to change

# **MASTER TL5 High Output**

SAP numerator – quantity per pack	1		
EAN/UPC — Product/Case	8711500639585		
Numerator – packs per outer box	40		


<b>EAN/UPC - Case</b> 8711500867759
-------------------------------------

## Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/830	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
SLV/40					


#### Photometric data



Spectral Power Distribution Colour - MASTER TL5 HO 24W/830 SLV/40

## Lifetime






Life Expectancy Diagram - MASTER TL5 HO 24W/830 SLV/40

Life Expectancy Diagram - MASTER TL5 HO 24W/830 SLV/40

# **MASTER TL5 High Output**

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 24W/830 SLV/40



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.