



MASTER TL5 High Output

MASTER TL5 HO 24W/830 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information			
Cap-Base	G5 [G5]		
Features	na [Not Applicable]		
Flux measurement reference	Sphere		
Light Technical			
Color Code	830 [CCT of 3000K]		
Luminous Flux	1,700 lm		
Color Designation	Warm White (WW)		
Chromaticity Coordinate X (Nom)	0.44		
Chromaticity Coordinate Y (Nom)	0.403		
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	76 lm/W		
Color rendering index (CRI)	82		

Operating and Electrical			
Power Consumption	22.7 W		
Lamp Current (Nom)	0.295 A		
Controls and Dimension			
Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Bulb Shape	T5 [16 mm (T5)]		
Approval and Application			
Energy Efficiency Class	G		
Mercury (Hg) Content (Nom)	1.2 mg		
Energy Consumption kWh/1000 h	23 kWh		
EPREL Registration Number	423553		


Datasheet, 2023, April 16 data subject to change

MASTER TL5 High Output

Product Data	
Order product name	MASTER TL5 HO 24W/830 SLV/40
Full product name	MASTER TL5 HO 24W/830 SLV/40
Full product code	871150063958555
Order code	927928083055
Material Nr. (12NC)	927928083055


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500639585
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500867759

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/830	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
SLV/40					


Photometric data



Spectral Power Distribution Colour - MASTER TL5 HO 24W/830 SLV/40

Lifetime






Life Expectancy Diagram - MASTER TL5 HO 24W/830 SLV/40

Life Expectancy Diagram - MASTER TL5 HO 24W/830 SLV/40

MASTER TL5 High Output

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 24W/830 SLV/40



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.