



# MASTER TL5 High Output

## MASTER TL5 HO 24W/830 SLV/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Operating and Electrical	
Cap-Base	G5 [G5]	Power Consumption	22.7 W
Features	na [Not Applicable]	Lamp Current (Nom)	0.295 A
Flux measurement reference	Sphere		
Light Technical		Controls and Dimming	
Color Code	830 [CCT of 3000K]	Dimmable	Yes
Luminous Flux	1,700 lm		
Color Designation	Warm White (WW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.44	Bulb Shape	T5 [16 mm (T5)]
Chromaticity Coordinate Y (Nom)	0.403		
Correlated Color Temperature (Nom)	3000 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	76 lm/W	Energy Efficiency Class	G
Color rendering index (CRI)	82	Mercury (Hg) Content (Nom)	1.2 mg
		Energy Consumption kWh/1000 h	23 kWh
		EPREL Registration Number	423553

# MASTER TL5 High Output

Product Data	
Order product name	MASTER TL5 HO 24W/830 SLV/40
Full product name	MASTER TL5 HO 24W/830 SLV/40
Full product code	871150063958555
Order code	927928083055
Material Nr. (12NC)	927928083055


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500639585
Numerator - Packs per outer box	40
EAN/UPC - Case	8711500867759

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 24W/830 SLV/40	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm

## Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 24W/830 SLV/40

## Lifetime




Life Expectancy Diagram - MASTER TL5 HO 24W/830 SLV/40



Life Expectancy Diagram - MASTER TL5 HO 24W/830 SLV/40

# MASTER TL5 High Output

## Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 24W/830 SLV/40

