



MASTER TL5 High Output

MASTER TL5 HO 24W/840 UNP/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Product data

General Information		Color Rendering Index (Max)	
Cap-Base	G5 [G5]	Color Rendering Index (Max)	85
Life to 50% Failures Preheat (Nom)	30000 h	Color Rendering Index (Min)	80
Features	na [Not Applicable]	Color Rendering Index (Nom)	82
System Description	High Output	LLMF 2000 h Rated	96 %
LSF Preheat 2000 h Rated	99 %	LLMF 4000 h Rated	95 %
LSF Preheat 4000 h Rated	99 %	LLMF 6000 h Rated	94 %
LSF Preheat 6000 h Rated	99 %	LLMF 8000 h Rated	93 %
LSF Preheat 8000 h Rated	99 %	LLMF 12000 h Rated	92 %
LSF Preheat 16000 h Rated	97 %	LLMF 16000 h Rated	91 %
LSF Preheat 20000 h Rated	84 %	LLMF 20000 h Rated	90 %
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Power (Nom)	22.5 W
Luminous Flux (Nom)	1950 lm	Lamp Current (Nom)	0.295 A
Luminous Flux (Rated) (Nom)	1700 lm	Temperature	
Color Designation	Cool White (CW)	Design Temperature (Nom)	35 °C
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	87 lm/W		
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	76 lm/W		

MASTER TL5 High Output

Controls and Dimming

Dimmable Yes

Mechanical and Housing

Cap-Base Information Green Plate

Approval and Application

Energy Efficiency Label (EEL) A

Mercury (Hg) Content (Nom) 1.4 mg

Energy Consumption kWh/1000 h 25 kWh

Product Data

Full product code 871150063704855

Order product name MASTER TL5 HO 24W/840 UNP/40

EAN/UPC - Product 8711500637048

Order code 927928084018

Numerator - Quantity Per Pack 1

Numerator - Packs per outer box 40


Material Nr. (12NC) 927928084018

Net Weight (Piece) 52.000 g

ILCOS Code FDH-24/40/1B-L/P-G5-16/550

Warnings and Safety

Dimensional drawing




Product


MASTER TL5 HO 24W/840 UNP/40

TL5 HO 24W/840

Photometric data



LDPB_TL5-HO8_840-Spectral power distribution B/W



LDPO_TL5-HO8_840-Spectral power distribution Colour

MASTER TL5 High Output

Lifetime



LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

