



TUV T5

TUV 24T5 HO G5

TUV T5 lamps are single- or double-ended UVC (germicidal) lamps used in professional water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General information		Operating and electrical	
Base	G5	Power (Rated) (Nom)	61 W
Main Application	Disinfection	Lamp Current (Nom)	0.8 A
Useful Life (Nom)	9000 h	Voltage (Nom)	77 V
System Description	High Output (HO)		
Light technical		Mechanical and housing	
Color Code	TUV	Bulb Shape	T5 [T5]
Color Designation	- [Not Specified]		
Depreciation at Useful Lifetime	15 %	Approval and application	
		Mercury (Hg) Content (Nom)	5.5 mg


TUV T5

UV	
UV-C Radiation at 100 hr	18 W
Product data	
Order product name	TUV 24T5 HO G5
EAN/UPC - Product	8719514413207
Order code	365882
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	40
Material Nr. (12NC)	927928304014
Copy Net Weight (Piece)	0.134 lb



Dimensional drawing



Product	D	C
TUV 24T5 HO G5	5/8 in	26-5/8 in

TUV 24T5 HO G5

