



MASTER TL5 High Output

MASTER TL5 HO 54W/840 SLV/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | | Operating and Electrical | |
|------------------------------------|---------------------|-------------------------------|---------|
| Cap-Base | G5 | Power Consumption | 54.4 W |
| Features | na [Not Applicable] | Lamp Current (Nom) | 0.455 A |
| Flux measurement reference | Sphere | | |
| Light Technical | | Controls and Dimming | |
| Color Code | 840 [CCT of 4000K] | Dimmable | Yes |
| Luminous Flux | 4,500 lm | | |
| Color Designation | Cool White (CW) | Mechanical and Housing | |
| Chromaticity Coordinate X (Nom) | 0.38 | Bulb Shape | T5 |
| Chromaticity Coordinate Y (Nom) | 0.38 | | |
| Correlated Color Temperature (Nom) | 4000 K | Approval and Application | |
| Luminous Efficacy (rated) (Nom) | 83 lm/W | Energy Efficiency Class | G |
| Color rendering index (CRI) | 80 | Mercury (Hg) Content (Nom) | 1.2 mg |
| | | Energy Consumption kWh/1000 h | 55 kWh |
| | | EPREL Registration Number | 423564 |

MASTER TL5 High Output

| Product Data | |
|---------------------|------------------------------|
| Order product name | MASTER TL5 HO 54W/840 SLV/40 |
| Full product name | MASTER TL5 HO 54W/840 SLV/40 |
| Full product code | 871150064318655 |
| Order code | 927929084055 |
| Material Nr. (12NC) | 927929084055 |

| | |
|---------------------------------|---------------|
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500643186 |
| Numerator - Packs per outer box | 40 |
| EAN/UPC - Case | 8711500868831 |

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---------------------------------|---------|------------|------------|------------|------------|
| MASTER TL5 HO 54W/840 SLV/40 | 17 mm | 1,149.0 mm | 1,156.1 mm | 1,153.7 mm | 1,163.2 mm |

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 54W/840 SLV/40

Lifetime



Life Expectancy Diagram - MASTER TL5 HO 54W/840 SLV/40



Lumen Maintenance Diagram - MASTER TL5 HO 54W/840 SLV/40

MASTER TL5 High Output

Lifetime

Life Expectancy Diagram - MASTER TL5 HO 54W/840 SLV/40

