



MASTER TL5 High Output



MASTER TL5 HO 80W/840 1SL/40

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G5
Features	HO Alto® [High Output Alto]
Flux measurement reference	Sphere

Light Technical

Colour Code	840 [CCT of 4000K]
Luminous Flux	6,550 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	82 lm/W
Colour rendering index (CRI)	81

Operating and Electrical

Power Consumption	79.8 W
Lamp current (nom.)	0.530 A

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing

Bulb shape	T5 [16 mm (T5)]
------------	-----------------

Approval and Application

Energy Efficiency Class	G
Mercury (Hg) content (nom.)	1.2 mg
Energy consumption kWh/1,000 hours	80 kWh
EPREL registration number	423571


Product Data

Order product name	MASTER TL5 HO 80W/840 SLV/40
Full product name	MASTER TL5 HO 80W/840 1SL/40
Full EOC	871150071045155
Order code	71045155
Material no. (12 NC)	927929584057
SAP numerator – quantity per pack	1

MASTER TL5 High Output


EAN/UPC – Product/Case	8711500710451
Numerator – packs per outer box	40
EAN/UPC - Case	8711500868862

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 80W/840 SLV/40	17 mm	1,449.0 mm	1,456.1 mm	1,453.7 mm	1,463.2 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 HO 80W/840 SLV/40

Lifetime




Life Expectancy Diagram - MASTER TL5 HO 80W/840 SLV/40



Life Expectancy Diagram - MASTER TL5 HO 80W/840 SLV/40

MASTER TL5 High Output

Lifetime



Lumen Maintenance Diagram - MASTER TL5 HO 80W/840 SLV/40

