



MASTER TL5 High Output Xtra

MASTER TL5 HO Xtra 80W/840 1SL/20

Low-pressure high-output mercury discharge lamps with a tubular 16 mm envelope

Product data

General Information	
Cap base	G5 [G5]
Life to 50% failures preheat (nom.)	45000 h
System description	High Output (HO)
LSF Preheat 2000 h Rated	100 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	98 %
LSF Preheat 20000 h Rated	97 %
Light Technical	
Colour code	840 [CCT of 4,000 K]
Luminous flux (nom.)	7000 lm
Luminous flux (rated) (nom.)	6400 lm
Colour designation	Cool White (CW)
Luminous efficacy (@ max. lumen, rated) (nom.)	88 lm/W
Correlated colour temperature (nom.)	4000 K
Luminous efficacy (rated) (nom.)	80 lm/W
Color rendering index (max.)	85
Color rendering index (min.)	80
Color rendering index (nom.)	82
LLMF 2000 h Rated	96 %

LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %

Operating and Electrical

Power (Rated) (Nom)	79.8 W
Lamp current (nom.)	0.530 A

Temperature

Design temperature (nom.)	35 °C
---------------------------	-------

Controls and Dimming

Dimmable	yes
----------	-----

Mechanical and Housing

Cap base information	Green Plate
----------------------	-------------

Approval and Application

Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	3.0 mg


MASTER TL5 High Output Xtra

Energy Consumption kWh/1000 h	88 kWh
Product Data	
Full product code	871150026303205
Order product name	MASTER TL5 HO Xtra 80W/840 SLV/20
EAN/UPC – product	8711500263032
Order code	26303205
Local Code	80840XTRATL5

Numerator – quantity per pack	1
Numerator – packs per outer box	20
Material no. (12NC)	927929784026
Net weight (piece)	127.400 g
ILCOS Code	FDH-80/40/1B-L/P-G5-16/1450

Warnings and Safety

Dimensional drawing





TL5 HO Xtra 80W/840

Product

MASTER TL5 HO Xtra 80W/840 SLV/20

Photometric data





Lightcolour /840

Lightcolour /840



MASTER TL5 High Output Xtra

Lifetime



LDLE_TL5HO8Xa_0001-Life expectancy diagram

LDLE_TL5HO8Xa_0002-Life expectancy diagram



LDLE_TL5HO8Xa_0003-Life expectancy diagram

