



# MASTER TL5 High Output Xtra

## MASTER TL5 HO Xtra 80W/840 SLV/20

This TL5 lamp (tube diameter 16 mm) combines the advantages of a TL5 High Output lamp (TL5 HO lamps are optimized for installations requiring high light output and offer excellent lumen maintenance and color rendering) with a long and reliable lifetime. This results in extra-low maintenance costs and saves on expensive spot replacement. Main applications are places where lamp replacement costs and/or costs of disruption are high.

### Product data

General Information	
Cap-Base	G5 [ G5]
Life to 50% Failures Preheat (Nom)	45000 h
System Description	High Output
LSF Preheat 2000 h Rated	100 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	99 %
LSF Preheat 8000 h Rated	99 %
LSF Preheat 16000 h Rated	98 %
LSF Preheat 20000 h Rated	97 %
Light Technical	
Color Code	840 [ CCT of 4000K]
Luminous Flux (Nom)	7000 lm
Luminous Flux (Rated) (Nom)	6400 lm
Color Designation	Cool White (CW)
Luminous Efficacy (@ Max Lumen, Rated) (Nom)	88 lm/W
Correlated Color Temperature (Nom)	4000 K

Luminous Efficacy (rated) (Nom)	80 lm/W
Color Rendering Index (Max)	85
Color Rendering Index (Min)	80
Color Rendering Index (Nom)	82
LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Nom)	79.8 W
Lamp Current (Nom)	0.530 A
Temperature	
Design Temperature (Nom)	35 °C

# MASTER TL5 High Output Xtra

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Cap-Base Information	Green Plate
----------------------	-------------

## Approval and Application

Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Nom)	3.0 mg
Energy Consumption kWh/1000 h	88 kWh

## Product Data

Full product code	871150026303205
-------------------	-----------------

Order product name	MASTER TL5 HO Xtra 80W/840 SLV/20
--------------------	-----------------------------------

EAN/UPC - Product	8711500263032
-------------------	---------------

Order code	927929784026
------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	20
---------------------------------	----


Material Nr. (12NC)	927929784026
---------------------	--------------

Net Weight (Piece)	127.400 g
--------------------	-----------

ILCOS Code	FDH-80/40/1B-L/P-G5-16/1450
------------	-----------------------------

## Warnings and Safety

## Dimensional drawing




## Product


MASTER TL5 HO Xtra 80W/840 SLV/20

## TL5 HO Xtra 80W/840

## Photometric data





LDPB\_TL5HO8Xa\_840-Spectral power distribution B/W



LDPO\_TL5HO8Xa\_840-Spectral power distribution Colour



# MASTER TL5 High Output Xtra

## Lifetime



LDLE\_TL5HO8Xa\_0001-Life expectancy diagram

LDLE\_TL5HO8Xa\_0002-Life expectancy diagram



LDLE\_TL5HO8Xa\_0003-Life expectancy diagram

