



# MASTER PL-S 2 Pin



## MASTER PL-S 7W/840/2P 1CT/5X10BOX

MASTER PL-S is an efficient low-wattage compact fluorescent lamp, typically used for decorative and orientation purposes. The original Philips-invented bridge technology guarantees optimum performance in the application, enabling more light and higher efficacy than the bended technology. The 2-pin version is designed for operation on electromagnetic gear and is provided with a plug-in/pull-out lamp base

### Warnings and Safety

- Use only with electromagnetic control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position
- Dimming is not possible
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Luminous Efficacy (rated) (Nom)		57 lm/W
Cap-Base	G23	Color rendering index (CRI)		80
Flux measurement reference	Sphere	Operating and Electrical		
Life to 50% Failures (Nom)	10,000 hour(s)	Power Consumption	7.2 W	
Light Technical		Lamp Current (Nom)	0.175 A	
Color Code	840 [CCT of 4000K]	Controls and Dimming		
Luminous Flux	400 lm	Dimmable	No	
Color Designation	Cool White (CW)	Approval and Application		
Chromaticity Coordinate X (Nom)	0.38	Energy Efficiency Class	G	
Chromaticity Coordinate Y (Nom)	0.38			
Correlated Color Temperature (Nom)	4000 K			

# MASTER PL-S 2 Pin


Mercury (Hg) Content (Max)	1.4 mg
Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	423585

## Product Data

Order product name	MASTER PL-S 7W/840/2P 1CT/5X10BOX
Full product name	MASTER PL-S 7W/840/2P 1CT/5X10BOX
Full product code	871150026065970


Order code	927935684011
Material Nr. (12NC)	927935684011
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500260659
Numerator - Packs per outer box	50
EAN/UPC - Case	8711500260673

## Dimensional drawing



Product	D (max)	D1 (max)	A (max)	B (max)	C (max)
MASTER PL-S 7W/840/2P 1CT/ 5X10BOX	28 mm	13 mm	97 mm	113 mm	135 mm


## Photometric data



Spectral Power Distribution Colour - MASTER PL-S 7W/840/2P 1CT/5X10BOX


# MASTER PL-S 2 Pin

## Lifetime



Life Expectancy Diagram - MASTER PL-S 7W/840/2P 1CT/5X10BOX

Life Expectancy Diagram - MASTER PL-S 7W/840/2P 1CT/5X10BOX



Lumen Maintenance Diagram - MASTER PL-S 7W/840/2P 1CT/5X10BOX

