



# PL-Q 4 Pin

## PL-Q 28W/835/4P 1CT/10BOX

Compact fluorescent lamps with a quadrant-like shape

### Warnings and Safety

- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Lamp light technical and electrical characteristics are influenced by operating conditions, i.e. lamp ambient temperature and operating position as well as applied HF control gear
- Shorter lamp life when often switching and not well pre-heated electrodes
- Shorter lamp life when often switching and not well pre-heated electrodes
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information		Color rendering index (CRI)	
Cap-Base	GR10Q [GR10q]	81	
Flux measurement reference	Sphere		
Light Technical		Operating and Electrical	
Color Code	835 [CCT of 3500K]	Power Consumption	28.4 W
Luminous Flux	2,050 lm	Lamp Current (Nom)	0.320 A
Color Designation	White (WH)	Controls and Dimming	
Chromaticity Coordinate X (Nom)	0.409	Dimmable	Yes
Chromaticity Coordinate Y (Nom)	0.394	Approval and Application	
Correlated Color Temperature (Nom)	3500 K	Energy Efficiency Class	G
Luminous Efficacy (rated) (Nom)	73.2 lm/W	Mercury (Hg) Content (Max)	3 mg

PL-Q 4 Pin


Mercury (Hg) Content (Nom)	4 mg
Energy Consumption kWh/1000 h	29 kWh
EPREL Registration Number	423613

Product Data

Order product name	PL-Q 28W/835/4P 1CT/10BOX
Full product name	PL-Q 28W/835/4P 1CT/10BOX
Full product code	871150026967625


Order code	927939383540
Material Nr. (12NC)	927939383540
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500269676
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500269027

Dimensional drawing



Product	U (max)	D (max)	D1 (max)	C (max)	C1 (max)	F (max)	E (max)
PL-Q 28W/835/4P 1CT/10BOX	46.5 mm	18.9 mm	33 mm	203 mm	76 mm	41 mm	200 mm


Photometric data




Spectral Power Distribution Colour - PL-Q 28W/835/4P 1CT/10BOX

PL-Q 4 Pin

Lifetime



Lumen Maintenance Diagram - PL-Q 28W/835/4P 1CT/10BOX



Life Expectancy Diagram - PL-Q 28W/835/4P 1CT/10BOX

Life Expectancy Diagram - PL-Q 28W/835/4P 1CT/10BOX

