



# T8 900 Series Rapid Start

## F32T8/TL950 98CRI 25PK

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050


### Product data

General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		139 V
Life to 50% Failures (Nom)	15,000 hour(s)	Controls and Dimming	
Light Technical		Dimmable	Yes
Color Code	TL950 [CCT of 5000K (950)]	Mechanical and Housing	
Luminous Flux	2,000 lm	Bulb Shape	T-8
Color Designation	TL950	Approval and Application	
Correlated Color Temperature (Nom)	5000 K	Mercury (Hg) Content (Nom)	5.0 mg
Luminous Efficacy (rated) (Nom)	63.9 lm/W	Product Data	
Color rendering index (CRI)	98	Order product name	F32T8/TL950 SLV
Operating and Electrical		Full product name	F32T8/TL950 98CRI 25PK
Power Consumption	32 W	Order code	209056
Lamp Current (Nom)	0.265 A	Material Nr. (12NC)	927942009520
Wattage Equivalent	32 W	Numerator - Quantity Per Pack	1
Voltage (Nom)	139 V		

# T8 900 Series Rapid Start


EAN/UPC - Product/Case	046677209056
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677209051

## Dimensional drawing



<b>Product</b>
F32T8/TL950 SLV

## Photometric data



Spectral Power Distribution Colour - F32T8/TL950 SLV

