



TUV T5

TUV 24T5 HE 4P SE

TUV T5 lamps are single- or double-ended UVC (germicidal) lamps used in professional water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

| General information | |
|---------------------------------|--------------------|
| Main Application | Disinfection |
| Useful Life (Nom) | 9000 h |
| System Description | High Efficiency |
| Light technical | |
| Color Code | TUV |
| Color Designation | - [Not Specified] |
| Depreciation at Useful Lifetime | 15 % |

| Operating and electrical | |
|--------------------------|---------------------|
| Power (Rated) (Nom) | 33 W |
| Lamp Current (Nom) | 0.425 A |
| Voltage (Nom) | 78 V |
| Mechanical and housing | |
| Cap-Base Information | 4 Pins Single Ended |
| Bulb Shape | T5 [T5] |


TUV T5

| | |
|----------------------------|-------------------|
| Approval and application | |
| Mercury (Hg) Content (Nom) | 3.0 mg |
| UV | |
| UV-C Radiation at 100 hr | 12 W |
| Product data | |
| Order product name | TUV 24T5 HE 4P SE |
| EAN/UPC - Product | 8719514413214 |

| | |
|---------------------------------|--------------|
| Order code | 365924 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 32 |
| Material Nr. (12NC) | 927948204099 |
| Copy Net Weight (Piece) | 0.161 lb |

Do not place in trash -
dispose according to local,
state, or federal laws

Dimensional drawing



| Product | D | C |
|-------------------|----------|-----------|
| TUV 24T5 HE 4P SE | 13/16 in | 27-5/8 in |

TUV 24T5 HE 4P SE

