



TUV T5

TUV 48T5 HO 4P SE

TUV T5 lamps are single- or double-ended UVC (germicidal) lamps used in professional water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General information		Operating and electrical	
Main Application	Disinfection	Power (Rated) (Nom)	107 W
Useful Life (Nom)	9000 h	Lamp Current (Nom)	0.8 A
System Description	High Output (HO)	Voltage (Nom)	135 V
Light technical		Mechanical and housing	
Color Code	TUV	Cap-Base Information	4 Pins Single Ended
Color Designation	- [Not Specified]	Bulb Shape	T5 [T5]
Depreciation at Useful Lifetime	15 %		

TUV T5

Approval and application

Mercury (Hg) Content (Nom)	5.5 mg
----------------------------	--------

UV

UV-C Radiation at 100 hr	35 W
--------------------------	------

Product data

Order product name	TUV 48T5 HO 4P SE
--------------------	-------------------


EAN/UPC - Product	8719514413276
-------------------	---------------

Order code	365965
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	32
Material Nr. (12NC)	927948704099
Copy Net Weight (Piece)	0.243 lb



Do not place in trash -
dispose according to local,
state, or federal laws

Dimensional drawing



Product	D	C
TUV 48T5 HO 4P SE	13/16 in	45-9/16 in

TUV 48T5 HO 4P SE

