
# **PHILIPS** Lighting



# **MASTER TL5 Circular**

### MASTER TL5 Circular 22W/827 1CT/10

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omnidirectional light distribution. It is suitable for a wide range of professional and semiprofessional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

#### Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### **Product data**


General Information		Controls and Di
Cap-Base	2GX13 [2GX13]	Dimmable
Light Technical		Mechanical and
Color Code	827 [CCT of 2700K]	Bulb Shape
Luminous Flux	1,800 lumen	
Color Designation	Incandescent White	Approval and A
Correlated Color Temperature (Nom)	2700 K	Mercury (Hg) Cont
Luminous Efficacy (rated) (Nom)	82 lm/W	Energy Consumpti
Color rendering index (CRI)	82	
		Product Data
Operating and Electrical		Full product code
Power Consumption	22.3 W	Order product nam
Lamp Current (Nom)	0.300 A	Order code
		Numerator - Quan
		New Artes Bride

Controls and Dimming	
Controts and Dimining	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	C-T5 [C-T5 16 mm]
Approval and Application	
Mercury (Hg) Content (Nom)	2.5 mg
Energy Consumption kWh/1000 h	25 kWh
Product Data	
Full product code	871150064219625
Order product name	MASTER TL5 Circular 22W/827 1CT/10
Order code	927965082713
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	927965082713


#### MASTER TL5 Circular

Full product name	MASTER TL5 Circular 22W/827 1CT/10		
EAN/UPC - Case	8711500642202		
EAN/UPC - Product/Case	8711500642196		

#### **Dimensional drawing**




## Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 22W/827 1CT/10

#### Lifetime



Life Expectancy Diagram - MASTER TL5 Circular 22W/827 1CT/10


Product	D (max)	D (min)	E (min)	E (max)	l (min)	I (max)
MASTER TL5 Circular 22W/827	18 mm	14 mm	220 mm	230 mm	187 mm	197 mm
1CT/10						



Life Expectancy Diagram - MASTER TL5 Circular 22W/827 1CT/10

#### MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 22W/827 1CT/10



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, October 26 - data subject to change