



MASTER TL5 Circular

TL5C 22W/840 1CT/10

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omnidirectional light distribution. It is suitable for a wide range of professional and semi-professional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Color rendering index (CRI)	
Cap-Base	2GX13 [2GX13]		81
Nominal lifetime	12,000 hour(s)	Operating and Electrical	
Flux measurement reference	Sphere	Power Consumption	23.5 W
		Lamp Current (Nom)	0.300 A
Light Technical		Controls and Dimming	
Color Code	840 [CCT of 4000K]	Dimmable	Yes
Luminous Flux	1,800 lm	Mechanical and Housing	
Color Designation	Cool White (CW)	Bulb Shape	C-T5 [C-T5 16 mm]
Chromaticity Coordinate X (Nom)	0.38	Approval and Application	
Chromaticity Coordinate Y (Nom)	0.38	Energy Efficiency Class	G
Correlated Color Temperature (Nom)	4000 K		
Luminous Efficacy (rated) (Nom)	82 lm/W		

MASTER TL5 Circular


Mercury (Hg) Content (Max)	4 mg
Mercury (Hg) Content (Nom)	4 mg
Energy Consumption kWh/1000 h	24 kWh
EPREL Registration Number	423619

Product Data

Order product name	MASTER TL5 Circular 22W/840 1CT/10
Full product name	TL5C 22W/840 1CT/10
Full product code	871150064221925


Order code	166009
Material Nr. (12NC)	927965084013
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500642219
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500642226

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 22W/840 1CT/10	3/4 inch	9/16 inch	8-11/16 inch	9-1/16 inch	7-3/8 inch	7-3/4 inch



Photometric data



Spectral Power Distribution Colour - MASTER TL5 Circular 22W/840 1CT/10


MASTER TL5 Circular

Lifetime



Life Expectancy Diagram - MASTER TL5 Circular 22W/840 1CT/10

Life Expectancy Diagram - MASTER TL5 Circular 22W/840 1CT/10



Lumen Maintenance Diagram - MASTER TL5 Circular 22W/840 1CT/10

