



MASTER TL5 Circular 環形日光燈管

MASTER TL5 Circular 55W/840 1CT/10

16 mm 管徑的環形螢光燈管，可選擇各種直徑

安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	2GX13 [2GX13]
標稱使用壽命	12,000 h
通量測量參考	Sphere
照明技術	
色碼	841 [CCT of 4100K]
光通量	4,210 lm
色彩名稱	冷白光 (CW)
色度坐標 X (標稱)	0.38
色度坐標 Y (Nom)	0.38
相關色彩溫度 (規範)	4000 K
光效 (額定) (標準)	76 lm/W
演色性指數 (CRI)	81
運轉與電力	
耗電量	55.7 W
燈具電流 (標稱)	0.550 A


控制與調光	
可調光	是
機械與外罩	
燈泡形狀	C-T5 [C-T5 16 mm]
認證與應用	
節能省電等級	G
汞 (Hg) 含量 (最大)	4 mg
汞 (Hg) 含量 (標稱)	4 mg
能源消耗 kWh/1000 h	56 kWh
EPREL 註冊碼	423623
產品資料	
下訂產品名稱	MASTER TL5 Circular 55W/840 1CT/10
完整產品名稱	MASTER TL5 Circular 55W/840 1CT/10
完整產品代碼	871150064251625
訂單代碼	927965784013
材質 Nr. (12NC)	927965784013

MASTER TL5 Circular 環形日光燈管

分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8711500642516
分子 - 每一外盒包裝	10


EAN/UPC - 箱	8711500642523
-------------	---------------

二维绘图




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 55W/840 1CT/10	18 mm	14 mm	293 mm	305 mm	260 mm	272 mm

光度数据




Spectral Power Distribution Colour - MASTER TL5 Circular 55W/840 1CT/10

壽命




Life Expectancy Diagram - MASTER TL5 Circular 55W/840 1CT/10



Life Expectancy Diagram - MASTER TL5 Circular 55W/840 1CT/10

MASTER TL5 Circular 環形日光燈管

壽命



Lumen Maintenance Diagram - MASTER TL5 Circular 55W/840 1CT/10

