



MASTER TL5 Circular

MASTER TL5 Circular 55W/840 1CT/10

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omnidirectional light distribution. It is suitable for a wide range of professional and semi-professional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	2GX13 [2GX13]	0.550 A	
Nominal lifetime	12,000 hour(s)	Controls and Dimming	
Flux measurement reference	Sphere	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	841 [CCT of 4100K]	Bulb Shape	C-T5 [C-T5 16 mm]
Luminous Flux	4,210 lm	Approval and Application	
Color Designation	Cool White (CW)	Energy Efficiency Class	G
Chromaticity Coordinate X (Nom)	0.38	Mercury (Hg) Content (Max)	4 mg
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Nom)	4 mg
Correlated Color Temperature (Nom)	4000 K	Energy Consumption kWh/1000 h	56 kWh
Luminous Efficacy (rated) (Nom)	76 lm/W	EPREL Registration Number	423623
Color rendering index (CRI)	81	Product Data	
Operating and Electrical		Order product name	MASTER TL5 Circular 55W/840 1CT/10
Power Consumption	55.7 W		

MASTER TL5 Circular

Full product name	MASTER TL5 Circular 55W/840 1CT/10
Full product code	871150064251625
Order code	927965784013
Material Nr. (12NC)	927965784013
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500642516
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500642523

Dimensional drawing




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 55W/840 1CT/10	18 mm	14 mm	293 mm	305 mm	260 mm	272 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 55W/840 1CT/10

Lifetime




Life Expectancy Diagram - MASTER TL5 Circular 55W/840 1CT/10



Life Expectancy Diagram - MASTER TL5 Circular 55W/840 1CT/10

MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 55W/840 1CT/10

