



MASTER TL5 Circular

MASTER TL5 CIRCULAR 60W/840 1CT/10

16 mm tube diameter circular fluorescent lamps with a choice of various diameters

Product data

General Information	
Cap base	2GX13 [2GX13]
Life to 50% failures preheat (nom.)	12000 h
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	99 %
LSF Preheat 6000 h Rated	96 %
LSF Preheat 8000 h Rated	89 %
LSF Preheat 16000 h Rated	10 %
LSF Preheat 20000 h Rated	1 %


Light Technical	
Colour Code	840 [CCT of 4,000 K]
Lamp Luminous Flux 25°C EL (Nom)	5000 lm
Lamp Luminous Flux (Nom)	5000 lm
Colour Designation	Cool White (CW)
Colour Temperature, horizontal (Nom)	4000 K
Lamp Luminous Efficacy EM (Nom)	83 lm/W
Colour Rendering Index,horiz (Nom)	82
LLMF 2000 h Rated	91 %
LLMF 4000 h Rated	87 %
LLMF 6000 h Rated	84 %
LLMF 8000 h Rated	81 %
LLMF 12000 h Rated	77 %
LLMF 16000 h Rated	74 %
LLMF 20000 h Rated	72 %

Operating and Electrical	
Power (Rated) (Nom)	60.0 W
Lamp current (nom.)	0.470 A
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	4 mg
Energy Consumption kWh/1000 h	66 kWh

Product Data	
Full product code	871150064261525
Order product name	MASTER TL5 Circular 60W/840 1CT/10
EAN/UPC – product	8711500642615
Order code	64261525
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	927966084013
Net weight (piece)	0.140 kg
ILCOS Code	FSCH-60/40/1B-L/P-2GX13-16

MASTER TL5 Circular

Dimensional drawing




TL5-C 60W/840


Product

MASTER TL5 Circular 60W/840 ICT/10

Photometric data




Lightcolour /840




Lightcolour /840

Lifetime




LDLE_TL5-C8_0001-Life expectancy diagram



LDLE_TL5-C8_0002-Life expectancy diagram

MASTER TL5 Circular

Lifetime



LDLM_TL5-C8_0001-Lumen maintenance diagram

