



MASTER TL5 Circular



MASTER TL5 Circular 60W/840 1CT/10

This circular TL5 lamp (tube diameter 16 mm) offers extended design possibilities. The slim tube allows the creation of extremely flat luminaires and enables omnidirectional light distribution. It is suitable for a wide range of professional and semi-professional applications, and is ideal for use in shops, offices and public areas with unconventional layouts.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Lamp Current (Nom)	
Cap-Base	2GX13	0.470 A	
Flux measurement reference	Sphere	Controls and Dimming	
Light Technical		Dimmable	Yes
Color Code	840 [CCT of 4000K]	Mechanical and Housing	
Luminous Flux	5,000 lm	Bulb Shape	C-T5
Color Designation	Cool White (CW)	Approval and Application	
Chromaticity Coordinate X (Nom)	0.38	Energy Efficiency Class	G
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) Content (Max)	4 mg
Correlated Color Temperature (Nom)	4000 K	Mercury (Hg) Content (Nom)	4 mg
Luminous Efficacy (rated) (Nom)	83 lm/W	Energy Consumption kWh/1000 h	61 kWh
Color rendering index (CRI)	81	EPREL Registration Number	423625
Operating and Electrical		Product Data	
Power Consumption	60.6 W	Order product name	MASTER TL5 Circular 60W/840 1CT/10

MASTER TL5 Circular

Full product name	MASTER TL5 Circular 60W/840 1CT/10
Full product code	871150064261525
Order code	927966084013
Material Nr. (12NC)	927966084013
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500642615
Numerator - Packs per outer box	10
EAN/UPC - Case	8711500642622

Dimensional drawing




Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
MASTER TL5 Circular 60W/840 1CT/10	18 mm	14 mm	367 mm	379 mm	334 mm	346 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL5 Circular 60W/840 1CT/10

Lifetime




Life Expectancy Diagram - MASTER TL5 Circular 60W/840 1CT/10



Life Expectancy Diagram - MASTER TL5 Circular 60W/840 1CT/10

MASTER TL5 Circular

Lifetime



Lumen Maintenance Diagram - MASTER TL5 Circular 60W/840 1CT/10

