



# TUV T5

## TUV 64T5 HO 4P SE UNP/32

TUV T5 lamps are single- or double-ended UVC (germicidal) lamps used in professional water and air disinfection units. The small 16 mm diameter of the lamp allows for a small system design and design flexibility. TUV T5 lamps offer constant UV output over their complete lifetime, for maximum security of disinfection and high system efficacy.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.
- DANGER: Risk Group 3 Ultra Violet product. These lamps emit high-power UV radiation that can cause severe injury to skin and eyes. Avoid eye and skin exposure to unshielded product. Use only in an enclosed environment which shields users from the radiation.

### Product data

General Information	
Cap-Base	4PINSSINGLEENDED [4 Pins Single Ended]
Useful Life (Nom)	9.000 hour(s)
Light Technical	
Color Code	TUV
Color Designation	- [Not Specified]
Depreciation at Useful Lifetime	20 %

Operating and Electrical	
Power Consumption	140 W
Lamp Current (Nom)	0.8 A
Voltage (Nom)	175 V
Voltage (Nom)	175 V
Mechanical and Housing	
Bulb Shape	T16 [T 16mm]

## TUV T5

### Approval and Application

Mercury (Hg) Content (Nom) 5.5 mg

### UV

UV-C Radiation at 100 hr 50.6 W

### Product Data

Order product name TUV 64T5 HO 4P SE UNP/32

Full product name TUV 64T5 HO 4P SE UNP/32

Full product code 871150026131199

Order code 927971104099

Material Nr. (12NC) 927971104099

Local order code 9279-711-04099


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8711500261311

Numerator - Packs per outer box 32


EAN/UPC - Case 8711500261328

### Dimensional drawing



Product	D (max)	C (max)	A (max)
TUV 64T5 HO 4P SE UNP/32	19.3 mm	1,564.5 mm	1,555.2 mm

### Photometric data



Spectral Power Distribution Colour - TUV 64T5 HO 4P SE UNP/32

